

Notes for Users

Please refer to the following for additional information about your machine.

If scanning of originals is in progress, open and close the paper trays gently when loading paper in Trays 3 and 4. (For machines with Copy and Scanner functions)

Please note the following corrections to the manuals for this machine.

“Control Panel”, About This Machine

Error	Correction
[Stop] key Press to stop a job in progress.	This information is not relevant to this machine.

“Printing Stored Documents”, Copy/Document Server Reference

Error	Correction
Procedure for interrupting a print job	This information is not relevant to this machine.
Procedure for changing the number of sets	

“Specifications”, Copy/Document Server Reference

Error	Correction
First copy time: Less than <u>10</u> seconds	First copy time: Less than <u>13.5</u> seconds
Continuous copy speed: 90 copies per minutes (B&W/ <u>Color</u> , A4/LT ☐)	Continuous copy speed: 90 copies per minutes (B&W/ <u>Colour</u> , A4/LT ☐)
Maximum original size: A3☐ (297mm×420mm), <u>11×17</u>	Maximum original size: A3☐ (297mm×420mm), <u>11×17☐</u>
Copy size: SR A3☐ -A5☐☐, <u>11×17 ☐ -5½×8½☐, 12×18</u>	Copy size: SR A3☐ -A5☐, <u>12×18 ☐ -5½×8½☐</u>
Paper thickness: Multi bypass tray: 60 - <u>220g/m²</u>	Paper thickness: Multi bypass tray: 60 - <u>216g/m²</u>

Error	Correction
Reproduction Ratio: Reduce: 93%, 82%, 75%, 71%, 65%, <u>50%</u>	Reproduction Ratio: Reduce: 93%, 82%, 75%, 71%, 65%, 50%, <u>25%</u>
Resolution: Scan: <u>1200</u> dpi	Resolution: Scan: <u>600</u> dpi
*1 When copying A4□ original in black & white using 100% magnification, Tray 1, <u>the exposure glass, and the auto paper select.</u>	*1 When copying A4□ original in black & white using 100% magnification, Tray 1, <u>the exposure glass.</u>

