

Model: Model CM-P1a		Date: 8-Nov-05	No.: RG144001
Subject: Service manual correction		Prepared by: T.Shintani	
From: 1st Tech. Support Sec. Service Support Dept.			
Classification:	<input type="checkbox"/> Troubleshooting <input type="checkbox"/> Mechanical <input type="checkbox"/> Paper path <input type="checkbox"/> Other ()	<input type="checkbox"/> Part information <input type="checkbox"/> Electrical <input type="checkbox"/> Transmit/receive	<input checked="" type="checkbox"/> Action required <input type="checkbox"/> Service manual revision <input type="checkbox"/> Retrofit information

Please note the following changes:

1. Firmware update procedure

The firmware update procedure was changed as follows:

1) USB Port Update

The USB port can be used to update the printer firmware (in addition to the parallel and EWS ports).

- 1) Connect the printer to the PC with a USB cable.
- 2) Open the command prompt and go to the directory that has the new firmware.
- 3) Make sure all of these files are saved to the **same folder** in the PC.
 - usbprns.exe
 - Rom File
 - Reset file
- 4) Execute the **usbprns**<F/W filename> command.
- 5) Wait for the printer to finish the firmware update.

Note:

- When the printer starts to receive the data, the "Online" LED blinks.
 - When the printer starts to overwrite the firmware, the "Error" LED turns ON.
 - When the printer finishes overwriting the firmware, the "Error" LED blinks.
 - When the printer finishes the firmware update, **all LEDs blink**.
- 6) Turn the printer OFF/ON.
 - 7) Download the RESET file.

Note: See the procedure below.

2) Additional procedure (after firmware update)

Do the following procedure after you update the firmware in the field.

Note: This is to set the paper size, because this model does not have an LCD.

1. After you update the firmware, turn the main power OFF/ON.
2. For **Command Prompt (parallel port)**:
 - 1) Open the command prompt and go to the directory which has the "Reset File".
 - 2) Execute the **copy /b <reset file name> lpt1:** command.
 - 3) Wait until the Configuration Sheet is printed.
 - 4) Turn the printer main power OFF/ON.

3. For **Command Prompt (USB port)**:

Important: When you use the USB port, make sure to save the "Usbprn.exe" file.

- 1) Open the command prompt and go to the directory which has the "Reset File".
 - 2) Execute the **usbprns <reset file name>** command.
 - 3) Wait until the Configuration Sheet is printed.
 - 4) Turn the printer main power OFF/ON.

4. For **EWS (Embedded Web Server)**:

- 1) Select the "Maintenance" tab in the EWS menu.
 - 2) Select "Printer Firmware" in the Upgrade Firmware menu.
 - 3) Select the "Reset file" for the update from the Search menu.
 - 4) Press the Upgrade button.
 - 5) Wait until the Configuration Sheet is printed.
 - 6) Turn the printer main power OFF/ON.

Model: Model CM-P1a

Date: 8-Nov-05

No.: RG144001

2. Service Manual Corrections

Change the areas in **bold** and delete the areas ~~crossed out~~.

SPECIFICATIONS

1.1 General Specifications

Configuration	Desktop	
Paper size	A4/Lt	
Print Resolution	Maximum	1200 x 1200 dpi
	Default	600 x 600 dpi
	RET Chip	Supported
	Gray Scale Level	128 Gray
Print Speed	A4-20 ppm	
	Letter-22 ppm	
Duplex Print Speed	Not Supported	
First Print Speed	Stand-by: 10 seconds	
	Energy saver mode: 50 seconds	
Copy Paper Weight	Paper Tray	60-105 g/m ² (16-28 lb.)
	By-pass tray	52-162 g/m ² (14-43 lb.)
	Optional paper tray	60-105 g/m ² (16-28 lb.)
	Duplex	64-105 g/m ² (17-28 lb.)
Warm-up Time	42 seconds from energy saver mode	
Paper Input Size	Standard tray	A4/LT – A5
	By-pass tray	A4/LT – A6, Free size
	By-pass tray-Custom size paper	Length: 160 - 432 mm (5.8" - 17"), Width: 90 - 305 mm (3.5" - 12"), Com#10, C5, C6, DL. Monarch
	Optional Envelope Feeder	Com#10, C5, C6, DL. Monarch
	Optional paper tray unit Up to 2 units can be installed.	A4/LT – A5
Paper Input Capacity	Standard/Optional paper trays	250 sheets (80 g/m ² , 20 lb.) SCF: Second Cassette Feeder
	By-pass tray	Normal paper: 50 sheets (80 g/m ² , 20 lb.)
		Special paper: 5 sheets
Output Capacity (Maximum 151 sheets)	150 sheets (face down)	
	1 sheet (face up)	
Total Counter	Electric Counter	
Environmental Standard	US version: Energy Star Tier 1	
	EU version: BAM specifications	
Energy Saver Mode	Selectable 1/5/15/30/45/60 minutes	

Model: Model CM-P1a

Date: 8-Nov-05

No.: RG144001

1.3 Software Specifications

OS	Windows 95/98/NT4.0/2000/Me/XP Linux OS including Red Hat, Caldera, Debian, Mandrake, Slackware, SuSE, and Turbo Linux	
Printer driver	Compatibility	SPL
	Default	SPL
	Remote control panel	Supported
	Status monitor	USB: Supported Network: Supported Parallel: Not supported
	Languages	English, Korean , German, French, Spanish, Italian, Dutch, Portuguese, Russian, Swedish, Norwegian, Finnish, Danish, Chinese, Taiwanese
	Contents	Printer driver, Acrobat reader , Manual, Electronic registration.
Driver Function	Layout	1. Orientation: Portrait, Landscape, Rotate 180 degrees 2. Layout options: Type, pages per slide, page order. 3. Favorites
	Paper	1. Copies 2. Paper options: Size, source, type 3. Favorites
	Graphics	1. Resolution: 1200 dpi, 600 dpi 2. Toner save: Printer setting (on/off) 3. Advanced options 4. Favorites
	Extras	1. Watermark 2. Overlay 3. Output options (Print order, re-print when jammed) 4. Favorites
	Printer	1. Printer configuration: High altitude correction

Model: Model CM-P1a

Date: 8-Nov-05

No.: RG144001

1.4 Optional unit specifications

Paper tray unit	Capacity	250 sheets (Life: 150 K)
	Media	A4, A5, Letter, Legal, Executive, Oficio, Folio, ISO, B5, JIS B5
	Paper weight	16-24 lb (60-90 g/m ²)
Memory	Memory upgrade	Supported
	Memory type	SDRAM
	Memory unit	32 MB, 128 MB
Network	Option	10/100 Base Tx
	Protocol	SPX/IPX, TCP/IP, Ethertalk, SNMP, HTTP 1.1, DLC/LLC
	Operating system	MS Windows 98/NT/ME/2000/XP, SUN Solaris, HP-UX, SCO, Novell Netware, Macintosh
Hard Disk	Not Supported	
Mailbox	Not Supported	
Serial	Not Supported	
Local talk	Not Supported	

Model: CM-P1	Date: 12-Mar-10	No.: RG144002
--------------	-----------------	---------------

RTB Reissue

The items in bold italics have been corrected or added.

Subject: Firmware Release History(Engine)		Prepared by: Y. Gaman	
From: 2nd Overseas Tech Support Sec., 2nd PQM Dept.			
Classification:	<input type="checkbox"/> Troubleshooting	<input type="checkbox"/> Part information	<input type="checkbox"/> Action required
	<input type="checkbox"/> Mechanical	<input type="checkbox"/> Electrical	<input type="checkbox"/> Service manual revision
	<input type="checkbox"/> Paper path	<input type="checkbox"/> Transmit/receive	<input type="checkbox"/> Retrofit information
	<input type="checkbox"/> Product Safety	<input checked="" type="checkbox"/> Other (Firmware)	<input checked="" type="checkbox"/> Tier 2

This RTB has been issued to announce the firmware release information for the **Engine**.

Version	Program No.	Effective Date
<i>6.04</i>	<i>G145604</i>	<i>August 2007 production</i>
6.01	G145601	1st Mass production

Version	Symptom Corrected
<i>6.04</i>	<i>Minor bug correction</i>
6.01	1st Mass production